136 Multi-Coloured LED Shooting Star Rope Light

Description

Used for Indoor or outdoor. 8 Function Memory Controller. Ensure that the mains connector must only be plugged into an interior power socket or an IP44 rated outdoor enclosure.

Specifications

Input Voltage	: 100V to 240V ~50/60Hz
PSU Output	: 36V, 100mA, 3.6W
Set Rating	: 36V DC, 3.4W
Number of LEDs	: 136

Part Number Table

Description	Part Number
136 Multi-Coloured LED Shooting Star Rope Light, 90cm	PEL01318

Important Notice : This data sheet and its contents (the “Information”) belong to the members of the AVNET group of companies (the “Group”) or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group’s liability for death or personal injury resulting from its negligence. pro-ELEC is the registered trademark of Premier Farnell Limited 2019.