

## Product information

# 00 21 20

## Tool Case "Vision24" Electric



### Well sorted and tidy: the standard tool case with versatile basic equipment

- With 20 brand tools, partly VDE tested according to DIN EN/IEC 60900
- Max. payload: 20 kg
- Volume: 24 litres
- Flexible options due to the individual partitioning of the inserts in the 60 mm deep base tray and its cover plate with six large tool compartments
- Tough ratchet hinges hold the lid open where necessary despite the deadweight of the tools
- Sturdy, ergonomic carrying handle, snaps into place at a 90° angle
- Removable tool board with 15 tool pockets on the base side and six tool pockets as well as a clamp compartment (400 mm wide) on the cover side, held by a push button
- Two lockable steel flip locks protect the case contents from theft
- With circumferential double aluminium frame
- Heavy duty ABS material, black
- Cover and tool boards made from dirt-repellent PP twin-wall sheets
- External dimensions (W x H x D): 480 x 380 x 180 mm; internal dimensions (W x H x D): 460 x 310 x 170 mm

### General

Article No.	00 21 20
EAN	4003773052166
Weight	7,055 g
Reach	yes
RohS	no

### Classification

eCl@ss 5.1.4	21100100
ETIM 5.0	EC000181
ETIM 6.0	EC000181
proficl@ss 6.0	EAA404c076
UNSPSC 13.1	27112117

### Content

03 06 180	1 x Combination Pliers ⚡1000V  
12 40 200	1 x Self-Adjusting Insulation Stripper (0,03 – 10,0 mm²) 
16 95 01 SB	1 x KNIPEX ErgoStrip® Universal Stripping Tool (Ø 8,0 – 13,0 mm) 
26 16 200	1 x Snipe Nose Side Cutting Pliers (Stork Beak Pliers) ⚡1000V   ⊖
26 26 200	1 x Snipe Nose Side Cutting Pliers (Stork Beak Pliers) ⚡1000V   $\leq 40^\circ$ ⊖
70 06 160	1 x Diagonal Cutter ⚡1000V 
74 06 160	1 x High Leverage Diagonal Cutter ⚡1000V 

<b>Content</b>	
86 03 180	1 x Pliers Wrench pliers and a wrench in a single tool 
86 03 180	1 x Pliers Wrench pliers and a wrench in a single tool 
87 03 250	1 x KNIPEX Cobra® High-tech Water Pump Pliers 
95 16 200	1 x Cable Shears with twin cutting edge (Ø 20 mm / 70 mm <sup>2</sup> ) ⚠1000V
98 20 25	1 x Screwdrivers for slotted screws (2,5 mm) ⚠1000V ⚡
98 20 40 SL	1 x Screwdriver (Slim) for slotted screws (4,0 mm) ⚠1000V ⚡
98 20 55 SL	1 x Screwdriver (Slim) for slotted screws (5,5 mm) ⚠1000V ⚡
98 20 65 SL	1 x Screwdriver (Slim) for slotted screws (6,5 mm) ⚠1000V ⚡
98 24 01 SL	1 x Screwdriver (Slim) for cross-recessed screws Phillips® (PH1) ⚠1000V ⚡
98 24 02 SL	1 x Screwdriver (Slim) for cross-recessed screws Phillips® (PH2) ⚠1000V ⚡
98 25 01 SL	1 x Screwdriver (Slim) for cross-recessed screws Pozidriv® (PZ 1) ⚠1000V ⚡
98 25 02 SL	1 x Screwdriver (Slim) for cross-recessed screws Pozidriv® (PZ 2) ⚠1000V ⚡
98 52	1 x Cable Knife ⚠1000V
005655	1 x Wera Voltage detector, single-pole 247 (0,5 x 3,0 x 70 mm)
<b>Accessories</b>	
00 21 20 LE	Tool Case "Vision24" empty,

*technical change and errors excepted*

*Con-Pearl® is a registered trade mark of friedola TECH GmbH*