

Product information

12 21 180

Insulation Stripper

With adapted blades

- With replaceable blades for 4 (adapted to diameters) or 6 (adapted to cross-sections) different conductor cross-sections
- Leave wire undamaged thanks to precision-ground blade shapes, even multi-stranded conductors are stripped gently
- During stripping, the wire is held firmly by clamping jaws
- With length stop for constant stripping length during repetitive work
- A spring leads the stripper back to the starting position
- Blade: special tool steel, oil-hardened
- Pliers body: aluminium



WW

General

Article No.	12 21 180
EAN	4003773000815
Pliers	black lacquered
Handles	with plastic grips
Weight	335 g
Dimensions	180 x 67 x 36 mm
Reach	no
RohS	no

Technical details

Stripping capacities in square millimetres	0.5 — 0.75 / 1.0 / 1.5 / 2.5 / 4.0 / 6.0 mm ²
AWG	20 — 18 / 16 / 14 / 12 / 10

Classification

eCl@ss 5.1.4	21040302
ETIM 5.0	EC000163
ETIM 6.0	EC000163
proficl@ss 6.0	AAA002c003
UNSPSC 13.1	27111510

Spare Parts

12 19 180 04	Insulation support (4) for 12 11/21 ...
12 19 180 18	Spring for number 16 (18),
12 29 180	1 pair of spare blades for 12 21 180,

technical change and errors excepted