

Product information

12 62 180

Automatic Insulation Stripper



Work faster: Adjusts automatically to most cable types, with fine adjustment for special materials

- Strips cables with standard materials without any need for manual adjustment
- Fine adjustable zero correction of the blade setting to special material requirements, e.g. due to large temperature differences
- Compact, handy and lightweight tool for common cable cross-sections and insulating materials
- For single, multiple and fine stranded cables of 0.2 up to 6 mm² with standard insulation
- Narrow head style for use in confined areas
- With wire cutter for copper and aluminium wires up to 2.5 mm²
- With adjustable length stop from 6.0 - 18.0 mm for constant stripping lengths
- Body: plastic, fibreglass-reinforced
- Blades: special tool steel, oil-hardened, interchangeable

AWA

General	
Article No.	12 62 180
EAN	4003773054573
Weight	151 g
Dimensions	180 x 75 x 21 mm
Reach	no
RohS	no
Technical details	
Stripping capacities in square millimetres	0.2 — 6.0 mm ²
AWG	24 — 10
Classification	
eCl@ss 5.1.4	21040302
ETIM 5.0	EC000163
ETIM 6.0	EC000163
proficl@ss 6.0	AAA002c003
UNSPSC 13.1	27111510
Spare Parts	
12 69 21	1 pair of spare blades for 12 62 180,
12 69 23	Spare length stop for 12 62 180,

technical change and errors excepted

