

Product information

35 12 115 ESD

Electronics Pliers ESD

DIN ISO 9655 DIN EN 61 340-5



- Precision pliers for fine assembly work, e.g. in electronics and fine mechanics
- For gripping, holding and bending
- Electrically discharging handles - dissipative
- Sturdy, zero backlash box joint
- Smooth ground gripping surfaces
- Edges carefully deburred
- Low-friction double spring for gentle and even opening
- The mirror polish together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- Handles with two-colour multi-component grips black/grey
- Flat, wide jaws
- Ball bearing chrome steel, oil hardened




General

Article No.	35 12 115 ESD
EAN	4003773024835
Head	mirror polished
Handles	with multi-component grips
Weight	70 g
Dimensions	115 x 68 x 17 mm
Standard	DIN ISO 9655 DIN EN 61 340-5
Reach	no
RohS	no

Technical details

Jaw length (B)	22.5 mm
Jaw thickness (joint) (D)	6.5 mm
Tips width (E)	2.0 mm
Tips thickness (F)	4.0 mm
Head width (A)	11.0 mm
ESD	yes



Classification

eCl@ss 5.1.4	21040301
proficl@ss 6.0	EAA840c015
UNSPSC 13.1	27112149

Spare Parts

35 99 01	Spare spring for electronics pliers, (2x)
----------	---

technical change and errors excepted

