

## Product information

# 49 11 A1

## Precision Circlip Pliers

For external circlips on shafts

DIN 5254 A



- Heavy duty in continuous operation: up to 10 times longer service life compared to turned tips
- With inserted tips for reliable work
- Large contact faces on the tips: no distortion of circlips, easy fitting
- Bolted joint: precise, zero backlash operation of pliers
- Internal opening spring, protected and captive
- Non-slip plastic coating on the handles
- Straight tips
- Inserted tips: spring steel wire, drawn
- Pliers body: chrome vanadium electric steel, forged, oil-hardened



General	
Article No.	49 11 A1
EAN	4003773048725
Pliers	grey atramentized
Handles	with non-slip plastic coating
Weight	100 g
Dimensions	140 x 64 x 11 mm
Standard	DIN 5254 A
Reach	no
RohS	no

Technical details	
Size of shaft	Ø 10 – 25 mm
Tips (diameter)	1.3 mm

Classification	
eCl@ss 5.1.4	21040301
ETIM 5.0	EC002228
ETIM 6.0	EC002228
proficl@ss 6.0	AAC470c002
UNSPSC 13.1	27112140

*technical change and errors excepted*



Spring inside the joint: the spring is protected inside the precisely bolted joint. It does not hinder work and cannot get dirty or lost.