

Product information

68 01 180

End Cutting Nipper

DIN ISO 5748

- The head shape provides optimised movement when tightening steel mesh knots during reinforced concrete work
- With cutting edges for soft and hard wire
- Also suitable for twisting and cutting binding wire
- Cutting edges additionally hardened; cutting edge hardness approx. 61 HRC
- High-grade special tool steel, forged, multi stage oil-hardened



General

Article No.	68 01 180
EAN	4003773013808
Pliers	black atramentized
Head	polished
Handles	plastic coated
Weight	284 g
Dimensions	180 x 52 x 15 mm
Standard	DIN ISO 5748
Reach	no
RohS	no

Technical details

Cutting capacities soft wire (diameter)	Ø 4.0 mm
Cutting capacities medium hard wire (diameter)	Ø 3.2 mm
Cutting capacities hard wire (diameter)	Ø 2.5 mm
Cutting edge length mm (C)	29 mm

Classification

eCl@ss 5.1.4	21040302
ETIM 5.0	EC002222
ETIM 6.0	EC002222
proficl@ss 6.0	AAA947c004
UNSPSC 13.1	27112117

technical change and errors excepted

