

Product information

71 22 200 T

KNIPEX CoBolt®

Compact Bolt Cutter



MM  $\angle 20^\circ$

Clever muscle man

- Opening spring and locking device are integrated in the handles also for comfortable work and protected transport
- With slim multi-component grips without collar for better handling and easier transport
- Pliers with tether attachment point for mounting a fall protection system
- With precision cutting edges for soft, hard and piano wire
- Cuts bolts, nails, rivets, etc. up to \varnothing 5.2 mm
- Efficient joint design ensures exceptional cutting performance with little effort
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 64 HRC
- 20° angled head with joint bar on one side and side cutter for almost flush cutting, with space for gripping
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened



General	
Article No.	71 22 200 T
EAN	4003773080053
Pliers	black atramentized
Handles	with slim multi-component grips, with integrated tether attachment point for a tool tether
Weight	370 g
Dimensions	200 x 55 x 23 mm
Reach	yes
RohS	no

Technical details	
Cutting capacities soft wire (diameter)	\varnothing 6 mm
Cutting capacities medium hard wire (diameter)	\varnothing 5.2 mm
Cutting capacities hard wire (diameter)	\varnothing 4.0 mm
Cutting capacities piano wire (diameter)	\varnothing 3.6 mm
Drop Protection System	yes

Classification	
eCl@ss 5.1.4	21040302
ETIM 5.0	EC002689
ETIM 6.0	EC002689
proficl@ss 6.0	AAC440c002
UNSPSC 13.1	27111512

Spare Parts	
71 19 200	Buffer spring,

technical change and errors excepted



20° angled head with single-sided joint bar and diagonal cutting edge for flush cutting; with space for gripping

