

## Product information

# 85 51 180 A

## Spring Hose Clamp Pliers



- Can be used for standard, space-saving and wire clamps, as well as for spring band clamps with a nominal size of up to 50 mm
- Allows more than 30 mm clamping range
- Rotating, universal grip inserts for reliably gripping the clamps in all positions
- Jaw inserts can also be rotated under load
- Extremely good leverage which allows clamps to be opened easily without great effort
- Slim head design; narrow head width, rotating grip inserts make this an ideal tool, especially in confined areas
- Additional function: detach hoses gently using the serrated jaw
- Chrome vanadium electric steel, forged, oil-hardened

### General

Article No.	85 51 180 A
EAN	4003773081159
Pliers	grey atramentized
Handles	with non-slip plastic coating
Weight	170 g
Dimensions	180 x 38 x 14 mm
Reach	no
RohS	no

### Technical details

Capacity	Ø max. 50 mm
Adjustment positions	15

### Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC000164
ETIM 6.0	EC000164
proficl@ss 6.0	AAA936c004
UNSPSC 13.1	27112112

### Spare Parts

85 59 250 A	Spare parts assortment grip inserts, for 85 51 250 A / 85 51 250 AF,
-------------	--

*technical change and errors excepted*



additional function: detach hoses gently using the serrated jaw



