

Product information

86 03 125

Mini pliers wrench

Pliers and a wrench in a single tool





- Replaces the need for sets of metric and imperial spanners
- Smooth jaws for damage free installation of plated fittings working directly on chrome!
- Also excellent for gripping, holding, pressing and bending workpieces
- Zero backlash jaw pressure prevents damage to edges of sensitive components
- Fast adjustment by pushing a button directly on the workpiece
- No unintentional shift of the gripping jaws and no slipping of the joint
- Parallel jaws give a more solid grip; its design allows flexible adjustment of all widths up to the specified maximum size
- The ratchet type principle allows quick and easy tightening and release of all bolted connections
- Lever transmission greater than 10: 1 for strong gripping power
- Chrome vanadium electric steel, forged, oil-hardened



General	
Article No.	86 03 125
EAN	4003773077497
Pliers	chrome-plated
Head	chrome-plated
Handles	plastic coated
Weight	105 g
Dimensions	125 x 35 x 13 mm
Reach	no
RohS	no

Technical details	
Jaw thickness (joint) (B2)	5.0 mm
Joint thickness (B3)	9.5 mm
Tips thickness (B1)	3.0 mm
Adjustment positions	11
Capacities for nuts	Ø 7/8 Inch
Capacities for nuts	23 mm




KNIPEX Quality – Made in Germany



eCl@ss 5.1.4 21043826 proficl@ss 6.0 AAA936c004 UNSPSC 13.1 27111560	Classification	
	eCl@ss 5.1.4	21043826
UNSPSC 13.1 27111560	proficl@ss 6.0	AAA936c004
	UNSPSC 13.1	27111560

Spare Parts	
87 09 125	Assortment of spare parts for adjustment for 86 / 87 125,

technical change and errors excepted



the mini pliers wrench for precision mechanics

