

Product information

87 01 250

KNIPEX Cobra®

High-tech Water Pump Pliers

DIN ISO 8976





You You Tube

- Push the button for adjustment on the workpiece
- Fine adjustment for optimum adaptation to different sizes of workpieces and a comfortable handle width
- Self-locking on pipes and nuts: no slipping on the workpiece and low handforce required
- Gripping surfaces with special hardened teeth, teeth hardness approx.
 61 HRC: high wear resistance and stable gripping
- Box-joint design for high stability due to double guide
- Reliable catching of the hinge bolt: no unintentional shifting
- Pinch guard prevents operators' fingers being pinched
- Chrome vanadium electric steel, forged, multi stage oil-hardened

| General | | |
|-----------------------|-------------------------------|--|
| Article No. | 87 01 250 | |
| EAN | 4003773022022 | |
| Pliers | grey atramentized | |
| Head | polished | |
| Handles | with non-slip plastic coating | |
| Weight | 335 g | |
| Dimensions | 250 x 44 x 14 mm | |
| Standard | DIN ISO 8976 | |
| Reach | no | |
| RohS | no | |
| - 1 1 1 1 4 11 | | |

| Technical details | |
|---------------------------------|---------|
| Adjustment positions | 25 |
| Capacities for nuts | Ø 2 |
| Capacities for nuts | 46 mm |
| Capacities for pipes (diameter) | Ø 50 mm |


| Classification | |
|----------------|------------|
| eCl@ss 5.1.4 | 21040301 |
| ETIM 5.0 | EC000164 |
| ETIM 6.0 | EC000164 |
| proficl@ss 6.0 | AAA936c004 |
| UNSPSC 13.1 | 27112112 |

| Spare Parts | |
|-------------|--|
| 87 09 01 | Assortment of spare parts for adjustment for 86/87 XX 250/300 (without 87 2X XXX), |

technical change and errors excepted

KNIPEX Quality – Made in Germany









 $\label{thm:continuous} \textbf{Teeth set against the direction of rotation have a self-locking effect and prevent slipping on the workpiece.}$









KNIPEX Quality – Made in Germany







