

Product information

90 10 185

Pipe cutter for multilayer and pneumatic hoses



Perfect cutting results: the hose and pipe cutter for professional users

- Ideal for all liquid, multilayer and pneumatic hoses/pipes commonly available on the market in the wide application range from Ø 4 - 20 mm
- With universal support for right-angled positioning
- Easy on the hands even in continuous use thanks to low force required and automatic opening thanks to the spring mechanism
- Exchangeable blade
- With opening spring and locking device
- Ergonomically shaped handles made of fibreglass-reinforced plastic
- Not suitable for cutting cables
- Blade made of high-strength special grade steel, oil-hardened and tempered



General

Article No.	90 10 185
EAN	4003773084846
Handles	tough fibreglass reinforced plastic handles
Weight	175 g
Dimensions	185 x 68 x 24 mm
Reach	no
RohS	no

Technical details

Cutting capacities (diameter)	Ø 4 – 20 mm
Cutting edge length mm	25 mm

Classification

eCl@ss 5.1.4	21040601
ETIM 5.0	EC000148
ETIM 6.0	EC000148
proficl@ss 6.0	AAB927c006

Spare Parts

90 29 01	Spare blade for 90 25 20 / 90 10 185 / 90 25 185,
----------	---

technical change and errors excepted

