

Product information

90 42 250

Punch Lock Riveter

- For one-hand operation
- To join metal section sheets used in dry walling for dividing walls and drop ceilings, without needing screws or rivets
- For U- and C-shaped sections with max 1.2 mm metal (2 x 0.6 mm)
- Minimum handforce required due to optimum lever transmission
- Pliers body: special tool steel, rolled, oil-hardened



MM

General

Article No.	90 42 250
EAN	4003773047865
Pliers	burnished
Handles	with multi-component grips
Weight	676 g
Dimensions	250 x 84 x 18 mm
Reach	no
RohS	no

Technical details

Capacity in millimetres	max. 1.2 (2 x 0.6)
-------------------------	--------------------

Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC011914
ETIM 6.0	EC011914
proficl@ss 6.0	EAC043c008
UNSPSC 13.1	27112115

technical change and errors excepted



The punching tool is squeezed through the metal section sheets



Setting the pliers for connection of two metal section sheets