

Product information

90 55 280

Sheet Metal Nibbler



- For cutting iron, copper or aluminium sheet metal up to max. 1.2 mm thickness, plastic up to max. 2.0 mm thickness
- Materials are cut without deformation
- Clean cut edges - no trimming activities needed
- With chip breaker
- Easy handling
- Cutting width: 2.7 mm
- Blades: special tool steel, oil-hardened, interchangeable
- Tool body: special tool steel, rolled, oil-hardened

AAA

General	
Article No.	90 55 280
EAN	4003773026730
Pliers	nickel plated
Handles	with multi-component grips
Weight	461 g
Dimensions	280 x 103 x 17 mm
Reach	no
RohS	no
Classification	
eCl@ss 5.1.4	21040302
ETIM 5.0	EC002149
ETIM 6.0	EC002149
proficl@ss 6.0	AAC441c002
UNSPSC 13.1	27112104
Spare Parts	
90 59 280	Spare blade for 90 55 280,
90 59 280 01	Metal cap for 90 55 280,
90 59 280 02	Opening spring for 90 55 280,

technical change and errors excepted

