

Product information

95 05 10 SB

Electricians' Shears



Universal shears with crimp area for electricians

- With crimp area for wire ferrules up to 6.0 mm²
- Precision finish with micro-toothing for a clean, non-slip cut
- Handles with multi-component grips, fibreglass-reinforced
- Cutting edges made from stainless steel, hardness of cutting edges 56 HRC
- With plastic belt pouch

General	
Article No.	95 05 10 SB
EAN	4003773082125
Head	polished
Handles	with multi-component grips, fibreglass-reinforced
Weight	135 g
Dimensions	160 x 130 x 32 mm
Reach	no
RohS	no

Technical details Capacity in square millimetres 6.0 mm² Classification

Classification		
eCl@ss 5.1.4	21040601	
ETIM 5.0	EC000160	
ETIM 6.0	EC000160	
proficl@ss 6.0	AAA520c003	

technical change and errors excepted



Securely stowed and always at hand



95 05 10 SB: Fast, easy crimping

KNIPEX Quality – Made in Germany





No slipping thanks to micro-serration







Integrated cable cutter






KNIPEX Quality – Made in Germany
















KNIPEX Quality – Made in Germany



