

Product information

95 06 230

Cable Shears

Handles extrusion plastic-coated

IEC 60900 DIN EN 60900



⚡ 1000 V

- For copper single conductors up to 16 mm², multiple stranded wires up to 50 mm², fine stranded up to 70 mm² and aluminium conductors multiple stranded wires up to 70 mm²
- Easy cutting with one-hand operation due to high transmission ratio
- Stainless - special grade - steel, oil-hardened and tempered
- Not suitable for steel wire and hard drawn copper conductors
- Precision-ground, hardened blades
- No crushing, slight deformation of the cable only
- Adjustable bolted joint
- Shears body: surgical steel, stainless, vacuum-hardened
- Handles: plastic, impact-proof

General

Article No.	95 06 230
EAN	4003773006305
Head	polished
Handles	plastic insulated, VDE-tested
Weight	274 g
Dimensions	230 x 82 x 30 mm
Standard	DIN EN 60900 IEC 60900
Reach	no
RohS	no

Technical details

Cutting capacity copper cable, multiple-stranded	50 mm ²
Cutting capacity copper cable, multiple-stranded	Ø 16 mm
AWG	1 / 0
VDE tested	yes

Classification

eCl@ss 5.1.4	21040601
ETIM 5.0	EC000142
ETIM 6.0	EC000142
proficl@ss 6.0	EAD256c001
UNSPSC 13.1	23241616

Spare Parts

95 09 230 01	Assortment of spare parts for 95 06 230,
--------------	--

technical change and errors excepted