

## Product information

**95 22 165**

### Cable Shears

With opening spring



- For cutting copper and aluminium single conductors as well as multiple stranded cables
- Clean and smooth cut without crushing and deformation
- Not suitable for steel wire and hard drawn copper conductors
- Precision-ground, hardened blades
- Easy cutting with one-hand operation
- With guard
- Adjustable bolted joint, self-retaining screw
- Internal opening spring, protected and captive
- High-grade special tool steel, forged, oil-hardened

///

#### General

Article No.	95 22 165
EAN	4003773069812
Shears	burnished
Handles	with multi-component grips
Weight	254 g
Dimensions	165 x 52 x 22 mm
Reach	no
RohS	no

#### Technical details

Cutting capacity copper cable, multiple-stranded	50 mm <sup>2</sup>
Cutting capacity copper cable, multiple-stranded	Ø 15 mm
AWG	1 / 0

#### Classification

eCl@ss 5.1.4	21040601
ETIM 5.0	EC000142
ETIM 6.0	EC000142
proficl@ss 6.0	EAD256c001
UNSPSC 13.1	23241616

*technical change and errors excepted*