

Product information

95 31 250

Cable Cutter (ratchet action)



- Fixed handle with support area for putting down the pliers when cutting
- For cutting copper and aluminium single conductors as well as multiple stranded cables
- Not suitable for steel wire, wire ropes and fine-stranded (highly flexible) conductors
- Precision-ground, hardened blades
- Clean and smooth cut without crushing and deformation
- One-hand operation using ratchet principle
- Little handforce required due to very high transmission ratio
- Two-stage ratchet drive for easy cutting
- Simple handling as a result of low weight and compact design - can be used even in confined areas
- Pinch guard prevents operators' fingers being pinched
- High-grade special tool steel, forged, oil-hardened

MM

General	
Article No.	95 31 250
EAN	4003773043935
Pliers	black lacquered
Handles	with multi-component grips
Weight	676 g
Dimensions	250 x 77 x 22 mm
Reach	no
RohS	no

Technical details	
Cutting capacity copper cable, multiple-stranded	240 mm ²
Cutting capacity copper cable, multiple-stranded	Ø 32 mm
MCM	500

Classification	
eCl@ss 5.1.4	21040301
proficl@ss 6.0	AAC484c002
UNSPSC 13.1	23241616

Spare Parts	
95 39 04	Feed pawl for 95 3 250/280,
95 39 03	Movable handle (3) for 95 31 250/280, with sleeve
95 39 05	Catch for 95 31 250/280,
95 39 06	Torsion spring for 95 31 250/280,
95 39 07	Pressure spring for 95 31 250/280,
95 39 08	Barrel spring for 95 31 250/280,
95 39 09	Set of catches for 95 31 250/280, 3-piece
95 39 10 97 N	Cover plate neutral,
95 39 11	Joint axis for 95 31 250/280,

Spare Parts

95 39 12	Set of distance bolts 3-piece,
95 39 12 97	Set of distance bolts 3-piece,
95 39 13	Raised countersunk screw,
95 39 13 97	Set of lock nuts,
95 39 04 280	Feed pawl,
95 39 97 280	Fixed cutter handle with sleeve,
95 39 250	Movable spare blade for 95 31 250 / 95 36 250,
95 39 99 250	Fixed cutter handle with sleeve,
95 69 190 03	Retainer,

technical change and errors excepted



