

## Product information

# 95 32 038

### Cable Shears

(ratchet action)

With telescopic handles



- Cable shears with adjustable telescopic handles allowing angular positioning
- For cable diameters up to 38 mm, handles can be positioned at an angle to set the optimum handle width, which makes the shear also suitable for work in confined areas
- Comfortable work thanks to ratchet action and low weight
- Heavy duty telescopic handles made of oval aluminium tubing; extendable up to 770 mm for maximum leverage on large cable diameters; retractable down to 570 mm for minimum space requirements during transport
- Replaceable cutting head
- Extensive cutting range up to max. Ø 38 mm or max. 280 mm<sup>2</sup> (e.g. 4 x 70 mm<sup>2</sup> NYN) in copper and aluminium cables
- Easier, neater cut due to optimised cutting edge geometry
- Adjustable bolted joint
- Handles: high-strength oval aluminium tubing
- Cutting head: special quality high-grade tool steel, oil-hardened

General	
Article No.	95 32 038
EAN	4003773071556
Head	burnished
Handles	with multi-component grips
Weight	1,980 g
Dimensions	570 x 160 x 45 mm
Reach	no
RohS	no
Technical details	
Cutting capacity copper cable, multiple-stranded	280 mm <sup>2</sup>
Cutting capacity copper cable, multiple-stranded	Ø 38 mm
MCM	550
Classification	
eCl@ss 5.1.4	21040601
ETIM 5.0	EC000142
ETIM 6.0	EC000142
proficl@ss 6.0	EAD256c001
UNSPSC 13.1	23241616
Spare Parts	
95 39 038	Spare cutter head for 95 32 038,

*technical change and errors excepted*

