

Product information

95 36 250

Cable Cutter (ratchet action)

IEC 60900 DIN EN 60900



⚡ 1000 V 

- For cutting copper and aluminium single conductors as well as multiple stranded cables
- Not suitable for steel wire, wire ropes and fine-stranded (highly flexible) conductors
- Precision-ground, hardened blades
- Clean and smooth cut without crushing and deformation
- One-hand operation using ratchet principle
- Little handforce required due to very high transmission ratio
- Two-stage ratchet drive for easy cutting
- Simple handling as a result of low weight and compact design - can be used even in confined areas
- Pinch guard prevents operators' fingers being pinched
- High-grade special tool steel, forged, oil-hardened

General

Article No.	95 36 250
EAN	4003773026884
Pliers	black lacquered
Handles	insulated with multi-component grips, VDE-tested
Weight	652 g
Dimensions	250 x 115 x 20 mm
Standard	DIN EN 60900 IEC 60900
Reach	no
RohS	no

Technical details

Cutting capacity copper cable, multiple-stranded	240 mm ²
Cutting capacity copper cable, multiple-stranded	Ø 32 mm
MCM	500
VDE tested	yes

Classification

eCl@ss 5.1.4	21040301
proficl@ss 6.0	AAC484c002
UNSPSC 13.1	23241616

Spare Parts

95 39 04	Feed pawl for 95 3 250/280,
95 39 08 S	Tension spring set for lateral mounting 95 36 25/28,
95 39 03	Movable handle (3) for 95 31 250/280, with sleeve
95 39 12	Set of distance bolts 3-piece,
95 39 13	Raised countersunk screw,
95 39 97 280	Fixed cutter handle with sleeve,

Spare Parts

95 39 250	Movable spare blade for 95 31 250 / 95 36 250,
95 39 99 250	Fixed cutter handle with sleeve,
95 69 190 03	Retainer,

technical change and errors excepted



Ratchet principle and two-stage ratchet drive for easier cutting