

Product information

95 36 320

Cable Cutter

(ratchet principle, 3-stage)

IEC 60900 DIN EN 60900



⚠ 1000 V 

- Sturdy. Easy to use. Stable.
- Innovative ratchet-drive.
- For cable up to Ø 60 mm
- Fixed handle with support area for putting down the pliers when cutting
- Easy handling due to low weight (825 g) and compact construction (320 mm length) - also usable in confined areas
- Cutting through copper and aluminium cables up to Ø 60 mm in one-hand and two-hand operation
- Hardened, precision-ground cutting edges cut smoothly and neatly without crushing
- For cutting copper and aluminium single conductors as well as multiple stranded cables
- Innovative three-stage ratchet-drive with high leverage for easy cutting in one-hand and two-hand operation
- Not suitable for steel wire, wire ropes and fine-stranded (highly flexible) conductors
- High-grade special tool steel, forged, oil-hardened

General

Article No.	95 36 320
EAN	4003773075189
Pliers	black atramentized
Head	polished
Handles	insulated with multi-component grips, VDE-tested
Weight	830 g
Dimensions	320 x 188 x 39 mm
Standard	DIN EN 60900 IEC 60900
Reach	no
RohS	no

Technical details

Cutting capacity copper cable, multiple-stranded	600 mm ²
Cutting capacity copper cable, multiple-stranded	Ø 60 mm
MCM	1,200
VDE tested	yes

Classification

eCl@ss 5.1.4	21040301
proficl@ss 6.0	AAC484c002
UNSPSC 13.1	23241616

Spare Parts

95 39 07	Pressure spring for 95 31 250/280,
95 39 320 01	Pivot cutter repair kit for 95 32 320 and 95 36 320,
95 39 320 02	Fixed cutter repair kit for 95 32 320 and 95 36 320,
95 39 320 03	Repair kit ratchet drive,

Spare Parts

95 39 320 04

Screw connection repair kit,

technical change and errors excepted

