

Product information

97 50 01

Crimping Pliers for Scotchlok™ connectors

With side cutter

- For crimping plastic-insulated telecommunication or signal cables using the U-contact principle in single Scotchlok™ connectors
- No stripping necessary, U-shaped elements establish the connection
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 60 HRC
- With opening spring
- Vanadium electric steel; forged, oil-hardened



General

Article No.	97 50 01
EAN	4003773028239
Head	polished
Handles	plastic coated
Weight	135 g
Dimensions	155 x 70 x 15 mm
Reach	no
RohS	no

Technical details



Applications	Scotchlok™ single connector
Capacity (diameter)	Ø 0.4 – 1.1 mm
Number of crimping positions	1

Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC000168
ETIM 6.0	EC000168
proficl@ss 6.0	AAA946c003
UNSPSC 13.1	27112147

technical change and errors excepted

Scotchlock™ is a registered trademark of 3M Deutschland GmbH.