

Product information

97 51 12

Crimping Pliers for Western plugs



- Improved opening mechanism, optimised design, less weight
- Can be used to crimp 4-, 6- and 8-pin Western plugs
- For cutting and stripping unshielded ribbon telephone cables
- Precise crimping process thanks to parallel crimping
- Repetitive, high crimping quality due to integral lock (self-releasing mechanism)
- Optimum transmission of force due to lever action for fatigue-reduced operation
- For Western plug type RJ 10 (7.65 mm wide), RJ 11/12 (9.65 mm wide) and RJ 45 (11.68 mm wide) long design
- With length cutter and stripping knife for ribbon cables 6 and 12 mm length
- Head burnished, handles with two-colour multi-component grips
- With additional stripping device for round cables
- Chrome vanadium electric steel in special quality, oil-hardened

General

Article No.	97 51 12
EAN	4003773043188
Pliers	burnished
Handles	with multi-component grips
Weight	475 g
Dimensions	200 x 63 x 18 mm
Reach	no
RohS	no

Technical details



Capacity	RJ 10 (4-poles) 7.65 mm RJ 11/12 (6-poles) 9.65 mm RJ 45 (8-poles) 11.68 mm
Number of crimping positions	3
Range of applications	Western plugs

Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC000168
ETIM 6.0	EC000168
proficl@ss 6.0	AAA946c003
UNSPSC 13.1	27112147

Spare Parts

97 59 12	3 spare blades for 97 51 12,
----------	------------------------------

technical change and errors excepted