

Product information

97 52 33

KNIPEX PreciForce®

Crimping Pliers


- Consistently high crimping quality thanks to precision dies and forced locking mechanism (unlockable)
- Tools have been set precisely (calibrated) in the factory
- Optimum transmission of force thanks to toggle lever for fatigue-reduced operation
- Good handling thanks to favourable handle position, low weight, compact design and ergonomically shaped handles
- Chrome vanadium electric steel in special quality, oil-hardened



General

Article No.	97 52 33
EAN	4003773051862
Pliers	burnished
Handles	with multi-component grips
Weight	478 g
Dimensions	220 x 59 x 30 mm
Reach	yes
RohS	no

Technical details



Applications	non-insulated crimp terminals, tube and compression cable lugs in accordance with DIN 46234 and DIN 46235 and non-insulated crimp, butt and press connectors in accordance with DIN 46341 and DIN 46267
Capacity in square millimetres	0.5 — 10.0 mm ²
Number of crimping positions	4
AWG	20 — 8

Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC000168
ETIM 6.0	EC000168
proficl@ss 6.0	AAA946c003
UNSPSC 13.1	27112147

Spare Parts

97 59 20	Extension spring for 97 52 XX, small
97 59 21	Extension spring for 97 52 XX, large
97 59 20	Extension spring for 97 52 XX, small



Spare Parts

97 59 21

Extension spring for 97 52 XX, large

technical change and errors excepted