

Product information

97 52 36

KNIPEX PreciForce® Crimping Pliers

- Consistently high crimping quality thanks to precision dies and forced locking mechanism (unlockable)
- Tools have been set precisely (calibrated) in the factory
- Optimum transmission of force thanks to toggle lever for fatigue-reduced operation
- Good handling thanks to favourable handle position, low weight, compact design and ergonomically shaped handles
- Chrome vanadium electric steel in special quality, oil-hardened



General	
Article No.	97 52 36
EAN	4003773051893
Pliers	burnished
Handles	with multi-component grips
Weight	487 g
Dimensions	220 x 63 x 23 mm
Reach	yes
RohS	no

Technical details	
	
Applications	insulated terminals, plug connectors + butt connectors
Capacity in square millimetres	0.5 — 6.0 mm ²
Number of crimping positions	3
AWG	20 — 10

Classification	
eCl@ss 5.1.4	21040301
ETIM 5.0	EC000168
ETIM 6.0	EC000168
proficl@ss 6.0	AAA946c003
UNSPSC 13.1	27112147

technical change and errors excepted



97 52 36