

Product information

97 71 180

Crimping Pliers for wire ferrules



- Light and slim design
- Also as VDE version
- Easy crimping due to optimised transmission ratio
- For crimping wire ferrules according to DIN 46228 parts 1 + 4 from 0.25 to 16 mm²
- Crimping in marked half-round dies for reliable connections between the sleeve and the conductor
- 9 particularly deep dies with conical side faces
- Special tool steel, forged, oil-hardened

General

Article No.	97 71 180
EAN	4003773040668
Head	polished
Handles	plastic coated
Weight	205 g
Dimensions	180 x 49 x 15 mm
Reach	no
RohS	no

Technical details



Applications	Wire ferrules
Capacity in square millimetres	0.25 — 16.0 mm ²
Number of crimping positions	9
AWG	24 — 6

Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC000168
ETIM 6.0	EC000168
proficl@ss 6.0	AAA946c003
UNSPSC 13.1	27112147

technical change and errors excepted

