

KNIPEX Quality – Made in Germany



New ranges of  
equipped cases



[www.knipex.com](http://www.knipex.com)



# **KNIPEX L-BOXX® Electric**

65 part






































**00**  
21

- ▶ **Strong box made of impact- and shock-proof ABS plastic**
- ▶ **With 14 KNIPEX tools and other brand name tools**
- ▶ **For mobile deployment**

- > Equipped with 65 brand name quality tools, some VDE-tested according to DIN EN 60900
- > Several boxes can be securely joined together
- > Flexible inner partitions
- > With two-part tool holder made of hard-wearing polyester fabric
- > Tool holders are connected to each other using hook-and-loop
- > Handle can be lowered into a hollow in the lid to save space
- > Ergonomically shaped handles with additional moulded recess on the side for flexible, convenient handling
- > strong box made of impact- and shock-proof ABS plastic
- > Dimension exterior (interior) width 442 (375) mm
- > Dimension exterior (interior) height 151 (107) mm
- > Dimension exterior (interior) depth 357 (311) mm



**00 21 19 LB E**

Article No.	EAN 4003773-					Quantity	Nominal size	 g
00 21 19 LB E	081623		KNIPEX L-BOXX® Electric, 65 part			1		11400
			00 11 01	KNIPEX TwinKey®	Knipex	1		
		   	08 26 145	Needle-Nose Combination Pliers		1	145 mm	
			12 42 195	MultiStrip 10		1	195 mm	
		   	13 86 200	Pliers for Electrical Installation		1	200 mm	
			16 95 01 SB	KNIPEX ErgoStrip®		1	135 mm	
		    	26 26 200	Snipe Nose Side Cutting Pliers (Stork Beak Pliers)		1	200 mm	
		   	70 06 160	Diagonal Cutter		1	160 mm	
		   	74 06 200	High Leverage Diagonal Cutter		1	200 mm	
			86 03 180	Pliers Wrench		1	180 mm	
			87 01 180	KNIPEX Cobra® Hightech Water Pump Pliers		1	180 mm	
		 	97 53 04	Self-Adjusting Crimping Pliers for End Sleeves (ferrules)		1	180 mm	
		 	98 52	Cable Knife		1	185 mm	
		  	98 25 01 SL	Screwdriver (Slim) for cross-recessed screws , Pozidriv®		1	187 mm	
		   	98 20 35 SL	Screwdriver (Slim) for slotted screws		1		
			05003484001	16-part set of VDE interchangeable blades, slim	Wera	1		
			004018	8100 SA 8 Zyklop set of metal ratchets, 28 parts		1	1/4"	
			003760	Joker open-end wrench		1	10 x 13 mm	
			101-0300	Locksmith's hammer	Picard	1	300 g	
			361 252 1	Electrician's Chisel	Rennsteig	1	250x10mm	
			16135	Model 70 Electric spirit level	Stabila	1	430 mm	
			18115	Pocket Electric mini spirit level		1	68 mm	
00 21 19 LB	081616		KNIPEX L-BOXX®, empty					9400
00 21 19 LB WK	081609		KNIPEX L-BOXX® two-part tool holder					953

## Tool Case "BIG Twin" Electric

65 parts

00  
21

- ▶ Hard-wearing ABS hard-shell construction with aluminium frame and circular buffer protection
- ▶ With 14 KNIPEX tools and other brand name tools

- > Equipped with 65 brand name quality tools, some VDE-tested according to DIN EN 60900
- > hard-wearing ABS hard-shell construction with aluminium frame and circular buffer protection
- > comfortable handle and mounting device for a "Trolley" embedded in the bottom (available ordering ref. 00 21 40 T)
- > can be opened on one or both sides; bottom tray and cover can be opened independently
- > stands stable in any opening position due to lid-holders and hinge mechanisms on both sides, that register in a position of 45° and 90°
- > 3-digit lock and two flip-locks for fixation of the cover
- > removable document compartment and removable tool board, with 13 push-in compartments on one side
- > base tray, height 58 mm, can be subdivided by flexible inserts; cover plate with six large push-in compartments, can be fixed by popper
- > dimensions, exterior (W x H x D): 490 x 255 x 410 mm
- > dimensions, interior (W x H x D): 445 x (105 + 105) x 350 mm



00 21 40

Same equipment as KNIPEX L-BOXX® Elektro 00 21 19 LB E

## Tool Case "BIG Twin" Move Elektro

65-teilig

00  
21

- ▶ With integrated rollers and telescopic handle
- ▶ With 14 KNIPEX tools and other brand name tools

- > heavy duty ABS material, black
- > all-round aluminium frame and firmly mounted sturdy centre board, each side offering multi-purpose push-in facilities by elastic loops and 12 small pockets
- > pull-out handle embedded in the base and two integrated smooth in-line skater runners
- > 30 kg maximum load
- > can be opened on one or both sides (V form); base tray and cover can be partially or fully opened independently of each other; stands securely in all opening positions; the special runners are gentle on the floor and ensure stability
- > lockable
- > removable document compartment and removable tool panel with 13 tool pouches
- > base tray, height 60 mm, can be subdivided by flexible inserts; tool panel as cover plate with 13 tool pouches
- > dimensions, exterior (B x H x T): 490 x 270 x 410 mm
- > dimensions, interior (B x H x T): 445 x (105 + 105) x 330 mm



00 21 41

Same equipment as KNIPEX L-BOXX® Electric 00 21 19 LB E

Article No.	EAN 4003773-		g
00 21 40	081968	Tool Case "BIG Twin" Electric, same equipment as 00 21 19 LB E	11400
00 21 41	082118	Tool Case "BIG Twin" Move Elektro, with integrated rollers and telescopic handle, same equipment as 00 21 19 LB E	13250
00 21 40 T	062981	Trolley for rolling case transport, for 00 21 40	1200

- ▶ Strong box made of impact- and shock-proof ABS plastic
- ▶ With 14 KNIPEX tools and other brand name tools
- ▶ For mobile deployment

- > Equipped with 52 brand name quality tools, some VDE tested according to DIN EN 60900
- > Several boxes can be securely joined together
- > Flexible inner partitions
- > With two-part tool holder made of hard-wearing polyester fabric
- > Tool holders are connected to each other using hook-and-loop
- > Handle can be lowered into a hollow in the lid to save space
- > Ergonomically shaped handles with additional moulded recess on the side for flexible, convenient handling
- > strong box made of impact- and shock-proof ABS plastic
- > Dimension exterior (interior) width 442 (375) mm
- > Dimension exterior (interior) height 151 (107) mm
- > Dimension exterior (interior) depth 357 (311) mm



**00 21 19 LB 5**

Article No.	EAN					Quantity	Nominal size	g
<b>00 21 19 LB 5</b>	081630		KNIPEX L-BOXX® Plumbing, 52 parts			1		9400
			00 11 01	KNIPEX TwinKey®		1		
			26 16 200	Snipe Nose Side Cutting Pliers (Stork Beak Pliers)	Knipec	1	200 mm	
			74 06 180	High Leverage Diagonal Cutter		1	180 mm	
			86 03 250	Pliers Wrench		1	250 mm	
			87 01 250	KNIPEX Cobra® Hightech Water Pump Pliers		1	250 mm	
			87 01 400	KNIPEX Cobra® XL Hightech Water Pump Pliers		1	400 mm	
			98 20 35	Screwdrivers for slotted screws		1		
			98 20 55	Screwdrivers for slotted screws		1	5,5 mm	
			98 26 15	Screwdriver for Torx® screws		1		
			98 26 20	Screwdriver for Torx® screws		1		
			98 26 25	Screwdriver for Torx® screws		1		
			98 24 01	Screwdriver for cross recessed screws Phillips®		1		
			98 24 02	Screwdriver for cross recessed screws Phillips®		1		
			361 252 1	Electrician's Chisel	Rennsteig		250 x 10 mm	
			005655	Voltage detector, single-pole, 247	Wera		0,5 x 3,0 x 70 mm	
			004018	8100 SA 8 Zyklop set of metal ratchets, 28 parts			1/4"	
			003760	Joker open-end wrench			10 x 13 mm	
			022086	Set of hex key wrenches			1,5 - 10 mm	
			90958	Express key	Heyco		17 x 19 mm M 10	
			16640003	Safety cutter knife			18 mm	
			101-0300	Locksmith's hammer	Picard		300 g	
			340 250 1	Mason's Chisels	Rennsteig		250 mm	
			02281	Spirit level type 70	Stabila		30 cm	
			71510-000	Metre ruler (yardstick)	Picard		2 m	
			6135-0	Pipe cutter	Zenten		3 - 35 mm / 1/8 - 1 1/2"	
<b>00 21 19 LB</b>	081616		KNIPEX L-BOXX®, empty					9400
<b>00 21 19 LB WK</b>	081609		KNIPEX L-BOXX® two-part tool holder					953