



Product Code: PC928

Description: UK 5A Fused Moulded Plug to C13 IEC Lock Connector 3G
0.5mm² H05VV-F Cable Black - 1.8 Metre



General Information

Complete Powerlead Rating	5A/250V	
	Fully Moulded UK Plug	C13 Connector
Component Rating	5A 250V~	10A 250V~
Colour	Black	Black
Materials	Over Moulding Cover: PVC Pins and Connecting Plate: Brass Fuse Clip: Bronze Belt	Terminal Housing, Handle: Nylon (PA66) Over Mould: PVC
Cable Colour	Black	
Number of Conductors	3	
Conductor Cross Sectional Area	0.75mm²	
Number of Strands	43	
Conductor Material	Bare Copper (99.97%)	
Jacket Material	PVC	
Jacket Wall Thickness	0.8mm	
Jacket Elongation	150%	
Insulation Material	PVC (Colour Coded)	
Insulation Wall Thickness (mm)	0.6mm	
Insulation Elongation	150%	
Nominal Resistance	26 Ohm/Km	
Overall Cable Diameter	6.5mm	
Bend Radius	32.5°	
Rated Temperature	-15 to +70°C	
Cable Hanking	200mm Fig. 8	
Features	Class I protection	
Standards	BS 1363-1: 2016 +A1: 2018 BS1362: 1973 plus Amendments 1 & 2 DIN EN 50525-2-11: 2012-01 EN 50525-2-11: 2011 EN 60320-1: 2015	