



3M™ Dual Lock™ Reclosable Fastener Twin Pack SJ354D, Black, 25 mm x 5 m, 5.7 mm

Part Number SJ354D, Black, 5M X 25MM



- Bond to plastics, powder coated paints and other low surface energy materials
- Solve attachment challenges faced with different materials and surfaces
- Use with ease for a more durable result
- Opens and closes 1000 times before losing 50% of its original tensile strength

Details

- Bond to plastics, powder coated paints and other low surface energy materials
- Solve attachment challenges faced with different materials and surfaces
- Use with ease for a more durable result
- Opens and closes 1000 times before losing 50% of its original tensile strength
- High initial tack
- Suitable for indoor applications

3M™ Dual Lock™ Reclosable Fastener SJ3540 has a rubber based adhesive on the back of a black, polypropylene reclosable fastener. It's suitable for bonding many plastics, powder coated paints and other low surface energy materials. Our reclosable fastener has 40 mushroom shaped stems / cm² with a 5.8 mm engaged thickness.

Attach a variety of materials with 3M™ Dual Lock™ Reclosable Fastener SJ3540. Our fastener is designed to bond many plastics, powder coated paints and other low surface energy materials with its interlocking mushroom shaped stems. It's a Type 250 stem density polyolefin fastener that is backed with a rubber based pressure sensitive adhesive and has 250 stems per square inch. Our fastener has closure action life of 1000 times before losing 50% of its original strength, making it reliable, for longer.

Suggested Applications

- Apply to plastics, powder coated paints and other low surface energy materials
- Interior signage
- Decorative trim
- Office partitions
- Graphic attachment
- Access panels
- Specialty vehicles (interior attachments)
- L-bracket edging, repositionable shelving
- Hang signage