

## Accessories

WWW.easyupinc.com



	NO	Description	Pieces/ Bundle	Weight/ Bundle
Guy Wire Clamp	EZ 43 A	Fits masts up to 2-1/2 tubing, comes with 3 screw eye bolts	25	20 lbs.
Guy Wire	EZ 60 EZ60 A EZ 60 B	6/20 galvanized plastic coated clear BOXED 6/20 uncoated guy wire 6/18 uncoated guy wire	1,000 ft. 1,000 ft. 1,000 ft.	28 lbs. 18 lbs. 32 lbs.
Guy Wire Cover	EZ 62A	1/2" UV Yellow, 7' split pieces 1" UV Yellow, 7' split pieces	25 per box 15 per box	5 lbs. 5 lbs.
Roof Guy Wire Anchors	EZ 65	"Goat Heads" PER C PER M	100 500	5 lbs. 24 lbs.
Eye and Turnbuckle	EZ 50	1/4" x 5-1/4" (7-3/8" open)	500	60 lbs.
Ground Anchors	EZ 30 EZ 48	30" Anchor, 4" helix, 1/2" rod 48" Anchor, 6" helix, 11/16" rod	12 per package 6 per bundle	22 lbs. 40 lbs.
Lag Screws	EZ 47-S1 EZ 47-S3	1/4" x 2" hex washer head, fully threaded 1/4" x 2-1/2" hex washer head, fully threaded	Bagged - 100 Bulk - 1,0000 Bagged - 100	2.5 lbs. 25 lbs. 2.5 lbs.
	EZ 47-S1	1/4" x 2" hex washer head, fully threaded 1/4" x 2-1/2" hex washer head, fully threaded	Bagged - 100 Bulk - 1,0000 Bagged - 100	2.5 lbs. 25 lbs. 2.5 lbs.
Extra Feet	EZ 3F EZ 5F	Small Foot, 3" long, includes locknut & bolt Large Foot, 5" long, includes locknut & bolt	3 3	-



## Antenna Tripods



		TI I DOUS FASSUR	1-202-057	-5144
	NO	Description	Pieces/ Bundle	Weight/ Bundle
Tripods 1" Tubing	EZ22-2	2' high (2 bolts)	6	28 lbs.
(Real of All Control	EZ 22-2A		6	29 lbs.
		INCLUDES SUPPORTING CUP	O	25 153.
	EZ22-3	3' high (2 bolts) up to 32" spread	6	37 lbs.
	EZ 22-3A	3' high, fits masts up to 1-3/4" (6 bolts)	6	38 lbs.
		is might, me maste up to 1 s. 1 (e zente)	ŭ	00 1501
		INCLUDES SUPPORTING CUP		
Tripods 1-1/4" Tubing	FZ 48-3A	3' high, fits masts up to 1-3/4" (6 bolts) - up to 32" spread	4	32 lbs.
0000		INCLUDES SUPPORTING CUP		02 1.001
000	EZ 48-5A	5' high, fits masts up to 1-3/4" (6 bolts) - up to 48" spread	4	48 lbs.
		INCLUDES SUPPORTING CUP		
	EZ 48-5AW	5' high, fits masts up to 2-1/4" - up to 48" spread	4	50 lbs.
10' Roof Tower	EZ 40	Heavy-duty 10' high, fits masts up to 1-3/4" tubing	3	87 lbs.
	EZ 40W	Heavy-duty 10' high, fits masts up to 1-5/4' tubing	3	90 lbs.
		Thousy duty to high, his musts up to 2 1/4 tubing	0	50 153.
		10' towers have up to a 32" spread		
Tri/Jiffy Mount 1-1/4" Tubing	EZTRI-5	Tri-Mount, 3' high tripod with 5' double-footed mast	3	35 lbs.
n	EZTRI-10	Tri-Mount, 5' high tripod with 10' double-footed mast	3	66 lbs.
	[ F7 C) / 2	liff Marrie 2/ binb dauble footed recent with 10// lane		
	EZ SV-3 EZ SV-5	Jiffy Mount, 3' high double-footed mast with 18" legs Jiffy Mount, 5' high double-footed mast with 36" legs	_	
	EZ 3V-5	Jilly Moulit, 5 High double-looted mast with 56 legs	_	
Masting	EZ 5-16	5' mast, 16 gauge 1-1/4" tubing	20	85 lbs.
	EZ 5-18	5' mast, 18 gauge 1-1/4" tubing	20	65 lbs.
	1	10' mast, 16 gauge 1-1/4" tubing	10	90 lbs
	EZ 10-18		10	70 lbs
		1.660 masting, 18 guage available cut to size		
Pitch Pad Kits	EZ 46-3	For 2' and 3' tripods 1/4" x 2" lag	80	18 lbs.
	EZ 46-5	For 5' and 10' towers 5/6" x 2-1/2" lag	50	20 lbs.
	EZ 46-5W	l	50	18 lbs.
		COMPLETE WITH 6 LAG SCREWS, INDIVIDUALLY BAGGED		

## Antenna Mounts



	The second second		Diagon/	Maight/
	NO	Description	Pieces/ Bundle	Weight/ Bundle
Roof Mounts	EZ 17 EZ 17A EZ 19A EZ 19 EZ 19B	Economy roof mount, fits masts up to 1-3/8" tubing Economy roof mount, fits masts up to 1-7/8" tubing Heavy duty roof mount, fits masts up to 1-7/8" tubing Heavy duty roof mount, fits masts up to 1-3/8" tubing Heavy duty roof mount, fits masts up to 2-1/4" tubing	25 20 25 25	6 lbs. 30 lbs. 32 lbs. 30 lbs.
"Z"Chimney Mounts	EZ 28-24 EZ 28-36 EZ 29-24S EZ 28-36S		25 25 25 25 25	40 lbs. 45 lbs. 35 lbs. 40 lbs.
"Y" Chimney Mounts	EZ 29-24 EZ 29-36 EZ 29-24S EZ 29-36S	· · · · · ·	12 12 12 12	44 lbs. 48 lbs. 39 lbs. 43 lbs.
Wall Mounts	EZ 30-4 EZ 30-6 EZ 30-8	4 "W" type, 1-/1/4" x 1/8" galvanized BAGGED W/ HARDWARE 6 "Y" type, 1-/1/4" x 1/8" galvanized BAGGED W/ HARDWARE 8 "Y" type, 1-/1/4" x 1/8" galvanized BAGGED W/ HARDWARE	25 12 12	26 lbs. 31 lbs. 39 lbs.
	EZ 30-12 EZ 30-18 EZ 30-24	Deluxe with extra 3rd leg support - 12 "Y" type BOXED  Deluxe with extra 3rd leg support - 12 "Y" type BOXED  Deluxe with extra 3rd leg support - 12 "Y" type BOXED  (Wall mount kits Include all hardware)	1 1 1	4 lbs. 5 lbs. 6 lbs.
Ground Mounts	EZ 32 EZ 32A EZ 32B	Regular ground mount, stake and plate Heavy-duty, with welded guide pipe accepts 2-/1/4 Economy stake and plate	10 1 10	32 lbs. 4 lbs. 6 lbs.
	EZTS-50 EZTS-60	Free-standing ground mount - fits masts up to 2-1/4" Free-standing ground mount - fits masts up to 2-3/4"	1 1	7 lbs. 9 lbs.
Dish Mounts	EZ DM 166-2 EZDW 166-2Z	Dish mount with 1.660" mast 18" long, gray powder coated  Dish mount with 1.660" mast 18" long, zinc plated  (Other mast sizes also available)	1	2.5 lbs. 2.5 lbs.
Eave/Vent Mounts	EZ 31	Heavy -duty adjustable eave mount, zinc clear coat Adjusts 45" - 60". eave/vent mounts Include all hardware.	1	7 lbs.
	EZ 70 EZ70W	Vent Mount - for vents 2-1/4" to 3-/3/4"  Vent Mount - for vents 2.5" to 5.5 inches	15 15	36 lbs. 36 lbs.



P/N	Description	Weight
EZTM - 20 EZTM - 30 EZTM - 30-U EZTM - 40 EZTM - 40 -U EZTM - 50	Telescoping mast - 231" (19' 3") Telescoping mast - 336" (28') Telescoping mast - 291" (24' 3") Telescoping mast - 435" (36' 3") Telescoping mast - 375" (31' 3") Telescoping mast - 528" (44')	25 lbs. 32 lbs. 30 lbs. CAN SHIP UPS 42 lbs. 40 lbs. CAN SHIP UPS 45 lbs.
EZ-HD-PTP-8	Heavy duty pole to pole mount Includes - 4 HD aligator clamps 2 - 8" Thredded Rods - 8 - KEPS Nuts	
EZ-EC-PTP-8	Economy pole to pole mount Includes 4 - clips, 2 - 4" Threadded Rods 6 - FLG Nuts	
EZ-GW-Kit	Guy wire kit Includes 50' of 6/20 plastic coated guy wire, guy clamp, 3 s hooks, 3 turnbuckles & 6 tiller clamps	

EZ - G - 6 Kit



Copper Grounding Kit.

Includes 4' copper plated rod, 1- 5/8" U bolt & saddle, 5/8" ground rod clamp & 6' #6 AWG bare copper strong wire



Easy Up Inc. P.O. Box 189 Kenosha, WI 52141-0189

Plant Location: 1325 - 56th St. Kenosha, WI

FAX 262-657-3144 PHONE 262-657-3144 WEB SITE: easyupinc.com