

CREALITY

MPN - CR-200B

Description – High – performance fully enclosed desktop 3D Printer

CR-200B 3D Printer



200*200*200 Printing Size

Fully Enclosed Design for Stable Printing

Intuitive Touchscreen Interface

Product Parameters

Molding technology: FDM	Number of nozzle: 1
Print size: 200 X 200 X 200mm	Hotbed temperature: ≤100℃
Machine dimension: 411 X 435 X 503mm	Nozzle temperature: ≤260℃
Package dimension: 533 X 499 X 605mm	Layer thickness: 0.1mm-0.4mm
N.W.: 16kg	Supported filament: PLA/ABS
G.W.: 20.68kg	Display: 4.3 inch color touch screen
Printing precision: ±0.1mm	Power supply: Input: 115-235V Output: 24V
Diameter of nozzle: 0.4mm	