

CREALITY

MPN - SERMOON D1

Description –Transparent and elegant 3D Printer

Sermoon D1 3D Printer



Transparent Appearance for Panoramic View

Stable Structure with Dual Z-Axis

280*260*310mm Large Printing Size

Product Parameters

Molding technology: FDM	G.W.: 25.5kg
Layer thickness: 0.1mm-0.4mm	Hotbed temperature: ≤100℃
Print size: 280 X 260 X 310mm	Number of nozzles: 1
Machine size: 500 X 500 X 531mm	Display: 4.3-inch touch screen
Package size: 590 X 590 X 395mm	Language: Chinese/English
Power supply: AC 100-240V, DC 24V	Printing accuracy: ±0.1mm
N.W.: 20.5kg	Nozzle temperature: ≤260℃
Nozzle diameter: Standard 0.4mm, optional 0.2mm/0.8mm/1.2mm	Supported filaments: PLA/ABS/TPU