

CREALITY

MPN - ENDER-5 PRO

Description - Ender-5 Pro 3D Printer



Removable Platform

double Y-axis control system

More smoothly Feed-in

Product Parameters

Molding technology	FDM
Printing size	220*220*300mm
Machine size	552*485*510mm
N.W. of machine	11.8KG
Number of nozzle	1
Slice thickness	0.1mm-0.4mm
Printing method	online or TF card offline
File format	STL/OBJ/AMF
Filament diameter	1.75mm
Printing precision	±0.1mm
Rated power	270W
Nozzle diameter	standard 0.4mm, optional 0.2/0.3mm
Power supply	rated voltage 115V/230V, output 24V
Operating system	Win XP/Vista/7/10/Mac/Linux
Slicing software	Cura/Repetier-Host/Simplify3D