

7 R 19

Combination ratchet spanner

Flat pattern

Code	ETIM
2297175	ECO02176 Maulringschlüssel
EAN	UNSPSC
4010886889268	27-11-17-13 Ring-Maulschlüssel
Country of Origin	eCl@ss
Germany	21-04-01-05 Ringmaulschlüssel
Customs tariff no.	
82041100	



Article description

- Flat pattern
- UD profile
- Working angle: 7° from 8 to 15 mm, 6° from 16 to 27 mm and 5° from 30 to 36 mm
- For ratchet loosening and fast tightening
- High torque transfer
- Hollow profile comfortable to hold
- Warp-resistant geometry with double T-girder effect
- GEDORE vanadium steel 31CrV3
- Non-glare look thanks to matt chrome-plating, locking insert and pawl manganese-phosphated
- Hot forged
- For ratchet loosening and fast tightening
- Ring 13° offset from shaft, reversible

Article information

Contents (Qty of pieces)	1 tlg.	REACH registration available	0
Total length [mm]	250 mm	Total width [mm]	44 mm
Total height [mm]	12 mm	Standard	not standardised
Net weight [kg]	0,202 kg	Width across flats [mm]	19,0
Material	31CrV3	Return angle	6°
Width of head 2 [mm]	42 mm	Head height 1 [mm]	11,7 mm
Head height 2 [mm]	6,4 mm	Width of head 1 [mm]	36,3 mm
Surface	chrome-plated	Jaw set	15°