

IN 20 4

Screwdriver bit socket 1/4"

for in-hex screws

Code	ETIM
6176280	ECO02157 Innensechskant-Einsatz für Steckschlüssel
EAN	UNSPSC
4010886617625	27-11-17-01 Schraubendreher
Country of Origin	eCl@ss
Germany	21-04-04-02 Schraubendrehereinsatz
Customs tariff no.	
82079030	



Article description

- Square drive as per DIN 3120 - C 6.3, ISO 1174, with ball retaining groove
- Hand-operated, knurled grip
- Chrome-plated
- Bit in GEDORE vanadium special steel, manganese-phosphated
- * not standardised
- Chrome-vanadium steel

Article information

Contents (Qty of pieces)	1 tlg.	Total width [mm]	12 mm
Total length [mm]	28 mm	Drive connector square female [inch]	1/4"
Net weight [kg]	0,011 kg	Working length	28,0 mm
Material	Chrome-vanadium steel	Tip length	16,0 mm
Width across flats 1 [mm]	4	Standard	DIN 3120 - C 6,3 ISO 1174 DIN 7422
Surface	chrome-plated	Insert Ø Actuator	12 mm
REACH registration available	0	Insert-Ø 1	12,0 mm
Drive connector square female (metric)	6,3 mm	Diameter 1 [mm]	12,0