

## 1993 U-3

### Reversible ratchet 1/2"

Code	ETIM
6144240	ECO02218 Umschaltknarre
EAN	UNSPSC
4010886614426	27-11-17-11 Ratschen
Country of Origin	eCl@ss
Germany	21-04-02-08 Antriebsteil (handbetätigt, Steckschlüsseinsatz)
Customs tariff no.	
82041100	



1/2" 12,5

#### Article description

- Acc. to DIN 3122, ISO 3315
- With non-slip metal disc change, fine-toothed (72 teeth) and robust
- Return angle 5 degrees
- Non-slip 2-component handle with hanging hole
- For hand-operated sockets and accessories with square drive as per DIN 3120 - C 12.5, ISO 1174, ball locking device
- GEDORE vanadium steel 31CrV3, chrome-plated
- GEDORE vanadium steel 31CrV3, chrome-plated

#### Article information

Contents (Qty of pieces)	1 tlg.	Total width [mm]	41 mm
Total length [mm]	270 mm	Standard	DIN 3122 ISO 3315
Total height [mm]	38 mm	Return angle	5°
Net weight [kg]	0,476 kg	Ratchet head height	40,5 mm
Drive connector square (male)	1/2"	Handle material	2-components
Drive connector square (male)	12,5 mm	Locking type	Ball locking device
Material	Chrome-vanadium steel 31CrV3	Push button release	0
Surface	chrome-plated	Number of teeth	72
REACH registration available	1		