

3093 U-10

Reversible ratchet 3/8"

Code	ETIM
6236950	ECO02218 Umschaltknarre
EAN	UNSPSC
4010886623695	27-11-17-11 Ratschen
Country of Origin	eCl@ss
Germany	21-04-02-08 Antriebsteil (handbetätigt, Steckschlüsseinsatz)
Customs tariff no.	
82041100	



Article description

- Acc. to DIN 3122, ISO 3315
- With recessed lever change
- Locks in the middle position: When the lever is flipped, it automatically engages for clockwise or counterclockwise operation
- Push-button release
- Return angle 11.25 degrees
- Non-slip 2-component handle with hanging hole
- For hand-operated sockets and accessories with square drive as per DIN 3120 - C 10, ISO 1174, ball locking device
- GEDORE vanadium steel 31CrV3, chrome-plated
- Vanadium steel 31CrV3, chrome-plated

Article information

Contents (Qty of pieces)	1 tlg.	Total width [mm]	35 mm
Total length [mm]	200 mm	Standard	DIN 3122 ISO 3315
Total height [mm]	30 mm	Return angle	11°
Net weight [kg]	0,254 kg	Ratchet head height	30,2 mm
Drive connector square (male)	3/8"	Handle material	2-components
Drive connector square (male)	10 mm	Locking type	Locking in middle position
Material	Chrome-vanadium steel 31CrV3	Push button release	1
Surface	chrome-plated	Shift type	Changeover lever
REACH registration available	1		