Switched Disconnects and Enclosures

Circuit-Lock® NEMA 3 and 3R Enclosures with Switch, 30A 2-Pole

HUBBELL

Features

- · All aluminum cover and base
- Flip-lid enclosure
- Ideal for use on outdoor equipment
- Surface mount control

Ordering Information

Description HBL7832D in NEMA 3R flip-lid enclosure, Ideal for use on outdoor equipment, Equipped with HBLFG30 sidewall insulation barriers

UPC Number 783585680934 **Catalog Number** HBL13R12



Listings

UL 508 CSA-C22.2 No.14

Specifications

Enclosure Material Water Ingress

Aluminum 3/3R

Performance

Electrical

Dielectric Voltage Electrical Life Max. Working Voltage **Short Circuit Current Ratings** (SCCR): (Motor Disconnect)

2,200V AC minimum for 1 minute Min. 6,000 Cycles at rated switch load 600V AC RMS

60A max. when protected by J fuses

Mechanical

Mechanical Life **Terminal Accommodations** Wire Type

10,000 minimum cycles #10 AWG Max.

Solid and stranded copper wire only


Environmental Flammability

Operating Temperature

UL94HB/VO

Max. Continous: 75°C: Min. Continuous: -40°C

without impact



Online Resources

Customer Use Drawing eCatalog

Installation Instructions

