



Features

- 22.2 V REMOVABLE LI-ION BATTERY FOR LONG LASTING POWER
- UP TO 40 MINUTES USAGE TIME ON 1 CHARGE
- 1.2L EASY-TO-EMPTY DUST CONTAINER
- WASHABLE HEPA FILTER, IDEAL FOR ALLERGY SUFFERERS
- INCLUDES MOTORISED FLOOR BRUSH WITH LED LIGHTS
- PERFECT FOR PET OWNERS
- COMPACT STORAGE WITH STORAGE HOOK
- HANDHELD UNIT- GREAT FOR USE ON STAIRS AND IN CAR
- ACCESSORIES INCLUDED: 2 IN 1 CREVICE AND BRUSH TOOL

3 YEAR GUARANTEE

Beldray^{est 1872}
AIRGILITY
CORDLESS

Up to 40 mins operating time
Clean your home floor to ceiling with just ONE charge

- CORDLESS & RECHARGEABLE**
Powerful, consistent suction
- 22.2 V REMOVABLE LI-ION BATTERY**
Provides long-lasting power
- 1.2 L EASY-TO-EMPTY DUST CONTAINER**
Effectively captures dirt and debris
- PERFECT FOR PET OWNERS**
Effortlessly removes pet hair

LED HEADLIGHTS
Within the motorised head for improved visibility

UP TO 40 MINUTES OPERATING TIME
Clean your home with just one charge

HANDHELD UNIT
Perfect for everyday clean ups

2 IN 1 CREVICE TOOL
For those hard to reach areas of the home

COMPACT STORAGE
Simply fits the body onto the storage hook

1.2 L EASY-TO-EMPTY DUST CONTAINER
Effectively captures dirt and debris

Good Housekeeping Institute APPROVED 2020

www.beldray.com

3 YEAR GUARANTEE

Beldray^{est 1872}
AIRGILITY
CORDLESS

Good Housekeeping Institute APPROVED 2020

Shipping Details / Product Details

Carton Qty: 3
Container Qty: 20 Ft: 780
40 Ft: 1632
40 HQ: 1848
Carton Details: 71.60l x 33.10w x 47.90h cm
CBM: 0.11
Carton Weight Net: 10.35 kg
Carton Weight Gross: 11.20 kg
Port: SHANGHAI

Product Code: BEL0776N
Packaging Type: Closed Colour Box
Box Size: 15.50l x 32.00w x 70.50h cm
Product Size: 22.00l x 25.00w x 117.00h cm
MOQ: 780
Barcode: 5054061102024
TUC: 05054061102031
Commodity Code: 8508 1100 00
Duty: 2.20%

FREE STOCK: 1,036
OFFER VALID FOR 14 DAYS

PRICE: £48.75
RRP: £149.99

Important:

The unit prices quoted on this document includes certification of the product to ensure compliance with mandatory UK and European legislation.
Please note: Any optional non-mandatory testing is not included in the quoted price. Any optional testing requirements, and subsequent cost revisions, must be agreed prior to an order being placed. Any optional testing requested after the order is placed will not be funded by Ultimate Products.

UP Global Sourcing T/A Ultimate Products

Unless otherwise agreed and confirmed in writing, this offer is subject to the standard terms and conditions of Ultimate Products.
These are available at www.upgs.com/terms.
Retail price provided for information only: retailers are free to set their own retail prices.

Ultimate Products UK Ltd.,
Manor Mill, Manchester OL9 0DD, UK
Tel: +44 (0)161 627 1400 Fax: +44 (0)161 628 2126
sales@upgs.com www.upgs.com