



- For indoor use
- Versatile cable ties can be used in countless applications
- One piece construction for consistent performance and reliability
- Lowest threading force of any one piece cable tie in the industry
- Curved tip is easy to pick up from flat surfaces and allows faster initial threading to speed installation

Part Number:	PLT2S-C*
Product Family:	<i>Pan-Ty</i> ® Colored Cable Ties - Standard
Product Line:	Nylon Cable Ties

RoHS Compliancy Status:	Compliant
-------------------------	-----------

Part Description:	Cable Tie, 7.4", Standard cross section
-------------------	---

Product Type:	Cable Ties
---------------	------------

Material:	Nylon 6.6
-----------	-----------

CSA Certified:	Yes
----------------	-----

Mil. Std. Part Number:	MS3367-1-2
------------------------	------------

UL Listed (File #E56854):	Yes
---------------------------	-----

UL Recognized (File #E56854):	Yes
-------------------------------	-----

Length (In.):	7.4
Length (mm):	188
Width (In.):	.190
Width (mm):	4.8
CE Compliant:	Yes
Cross Section:	Standard
Head Height (In.):	.220
Head Height (mm):	5.6
Head Width (In.):	.316
Head Width (mm):	8.0
Locking Style:	Locking
Material Flammability Rating:	UL94V-2
Max. Bundle Diameter (In.):	1.88
Max. Bundle Diameter (mm):	48
Max. Continuous Use Temperature:	185°F (85°C)
Min. Loop Tensile Strength (Lbs.):	50
Min. Loop Tensile Strength (N):	222
Std. Pkg. UOM:	PK
Thickness (In.):	.052

Thickness (mm):	1.3
Tool:	GTS, GTSL, GS2B, GTH, GS4H, PTS, PTH, PPTS, STS2, STH2
UOM:	PC
Std. Pkg. Qty.:	100
Min. Order Qty.:	100