

SALTER BEAN TO JUG COFFEE MAKER



Features

- SALTER BEAN TO JUG COFFEE MAKER
- 650 W POWER
- 750 ML CAPACITY GLASS CARAFE
- INTEGRATED STAINLESS STEEL GRINDER
- DIGITAL CONTROL PANEL WITH 24-HOUR TIMER
- ANTI-D RIP AND KEEP-WARM FUNCTIONS
- DUAL GRIND AND BREW FUNCTION
- AUTO SHUT-OFF FOR OPTIMAL SAFETY
- INCLUDES REUSABLE MESH FILTER



Shipping Details / Product Details

Carton Qty: 4
Container Qty:
20 Ft: 1224
40 Ft: 2596
40 HQ: 2832
Carton Details: 63.00l x 48.30w x 33.50h cm
CBM: 0.10
Carton Weight Net: 11.30 kg
Carton Weight Gross: 12.25 kg
Port: NINGBO

Product Code: EK4368
Packaging Type: Closed Colour Box
Box Size: 30.20l x 23.00w x 30.20h cm
Product Size: 25.80l x 17.80w x 27.60h cm
MOQ: 1224
Barcode: 5054061416220
TUC: 05054061424218
Commodity Code: 8516710000
Duty: 2.70%

FREE STOCK: 1,031
FREE COMMITMENT: 1,224
DATE OF FIRST PO: 09/05/2022
OFFER VALID FOR 14 DAYS

PRICE: £30.75
RRP: £99.99

Important:

The unit prices quoted on this document includes certification of the product to ensure compliance with mandatory UK and European legislation.
Please note: Any optional non-mandatory testing is not included in the quoted price. Any optional testing requirements, and subsequent cost revisions, must be agreed prior to an order being placed. Any optional testing requested after the order is placed will not be funded by Ultimate Products.

UP Global Sourcing T/A Ultimate Products

Unless otherwise agreed and confirmed in writing, this offer is subject to the standard terms and conditions of Ultimate Products. These are available at www.upgs.com/terms.
Retail price provided for information only: retailers are free to set their own retail prices.

Ultimate Products UK Ltd.
Manor Mill, Manchester OL8 0DD, UK
Tel: +44 (0)161 827 1400 Fax: +44 (0)161 628 2126
sales@upgs.com www.upgs.com

