

J.21LA | J.LA - 3/8" long-reach metric 12-point sockets



Standards:

NF ISO 2725-1, NF ISO 1711-1, ISO 2725-1, ISO 1711-1, DIN 3124, ASME B107.5

Description:

- OGV® profile: more powerful tightening, preserves fasteners.
- Long-reach sockets for long recess or thread access.
- Available as rack sets (Ref JL.40U).
- Finish: bright chrome.

	J.21LA
A [mm]	21.0
Diameter [mm]	24.0
Diameter D1 [mm]	27.0
Length L [mm]	60.0
Length L1 [mm]	18.0
12-Point [mm]	12.0
Weight [g]	123.0