

Product data sheet

Specifications

SQUARE D

Green Premium™



Industrial control transformer,
Type T, 1 phase, 150VA,
240/416/480/600V primary,
99/120/130V secondary, 50/60Hz

9070T150D50

Product availability : Stock - Normally stocked in distribution facility

Price* : 441.00 USD

Main

Product Type	Industrial Control Transformer
Power Rating	150 VA
Type	T

Complementary

Number of Phases	1 phase
Power Rating	150 VA
Temperature Rise	55 °C
Electrical Connection	Screw clamp terminals
Height	3.84 in (97.54 mm)
Width	4.5 in (114.30 mm)
Depth	4.74 in (120.40 mm)
Material	Copper winding
Fingersafe Cover Compatibility	FSC23

Environment

Certifications	UL listed file E61239 CSA file LR37055 guide 184-N-90
Enclosure Type	Not rated (open device)
Insulation Temperature	221 °F (105 °C)

Ordering and shipping details

Category	16206-9070 T (NOT TF) MTO
Discount Schedule	CP8
GTIN	785901327264
Nbr. of units in pkg.	1
Package weight(Lbs)	8.40 lb(US) (3.81 kg)
Returnability	Yes

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country of origin	US
-------------------	----

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	6.60 in (16.764 cm)
Package 1 width	6.30 in (16.002 cm)
Package 1 Length	7.80 in (19.812 cm)
Unit Type of Package 2	PAL
Number of Units in Package 2	150
Package 2 Weight	1381.24 lb(US) (626.52 kg)
Package 2 Height	40.00 in (101.6 cm)
Package 2 width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
PVC free	Yes

Contractual warranty

Warranty	10 Years
----------	----------