

# Product data sheet

Specifications

**SQUARE D**

**Green Premium™**



Low voltage transformer, encapsulated buck boost, 1 phase, 0.25kVA, 120x240V primary, 12/24V secondary, Type 3R

250SV43B

**Product availability : Stock - Normally stocked in distribution facility**

**Price\* : 361.00 USD**

## Main

|                        |                            |
|------------------------|----------------------------|
| Product                | Buck and Boost Transformer |
| Enclosure Code         | 4A                         |
| Enclosure Type         | NEMA 3R                    |
| Insulation Temperature | 266 °F (130 °C)            |
| Primary Voltage        | 120 x 240 V                |
| Power Rating           | 0.25 kVA                   |
| Secondary Voltage      | 12/24 V                    |
| Temperature Rise       | 80 °C                      |

## Ordering and shipping details

|                       |                        |
|-----------------------|------------------------|
| Category              | 16265-BUCK & BOOST     |
| Discount Schedule     | PE2                    |
| GTIN                  | 785901876151           |
| Nbr. of units in pkg. | 1                      |
| Package weight(Lbs)   | 9.71 lb(US) (4.404 kg) |
| Returnability         | Yes                    |
| Country of origin     | MX                     |

## Packing Units

|                        |                     |
|------------------------|---------------------|
| Unit Type of Package 1 | PCE                 |
| Package 1 Height       | 6.50 in (16.51 cm)  |
| Package 1 width        | 6.80 in (17.272 cm) |
| Package 1 Length       | 7.80 in (19.812 cm) |

## Offer Sustainability

|                           |   |
|---------------------------|---|
| Sustainable offer status  | Green Premium product   |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |

\* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

|                                   |   |
|-----------------------------------|---|
| <b>REACH Regulation</b>           | <a href="#">REACH Declaration</a>   |
| <b>REACH free of SVHC</b>         | Yes   |
| <b>EU RoHS Directive</b>          | Compliant<br><a href="#">EU RoHS Declaration</a>  |
| <b>Toxic heavy metal free</b>     | Yes   |
| <b>Mercury free</b>               | Yes   |
| <b>RoHS exemption information</b> | <a href="#">Yes</a>   |
| <b>China RoHS Regulation</b>      | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope) |
| <b>Environmental Disclosure</b>   | <a href="#">Product Environmental Profile</a>   |
| <b>PVC free</b>                   | Yes   |

## Contractual warranty

|                 |           |
|-----------------|-----------|
| <b>Warranty</b> | 18 months |
|-----------------|-----------|