

# Product data sheet

Specifications

SQUARE D

Green Premium™



Industrial control transformer,  
Type T, 1 phase, 75VA, 240x480V  
primary, 120V secondary, 50/60Hz

9070T75D1

Product availability : Stock - Normally stocked in distribution facility

**Price\* : 166.00 USD**

## Main

Product Type	Industrial Control Transformer
Power Rating	75 VA
Type	T

## Complementary

Number of Phases	1 phase
Power Rating	75 VA
Temperature Rise	55 °C
Electrical Connection	Screw clamp terminals
Height	2.89 in (73.41 mm)
Width	3.38 in (85.85 mm)
Depth	3.34 in (84.84 mm)
Material	Copper winding
Fingersafe Cover Compatibility	FSC1

## Environment

Certifications	CSA file LR37055 guide 184-N-90 UL listed file E61239
Enclosure Type	Not rated (open device)
Insulation Temperature	221 °F (105 °C)

## Ordering and shipping details

Category	16200-9070 T (NOT TF) 50-200VA
Discount Schedule	CP8
GTIN	785901904731
Nbr. of units in pkg.	1
Package weight(Lbs)	3.83 lb(US) (1.737 kg)
Returnability	Yes
Country of origin	MX

\* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.95 in (7.493 cm)
Package 1 width	3.35 in (8.509 cm)
Package 1 Length	3.38 in (8.585 cm)
Unit Type of Package 2	PAL
Number of Units in Package 2	450
Package 2 Weight	1725.55 lb(US) (782.696 kg)
Package 2 Height	40.00 in (101.6 cm)
Package 2 width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
PVC free	Yes

## Contractual warranty

Warranty	10 Years
----------	----------