

Product data sheet

Specifications

SQUARE D

Green Premium



Industrial control transformer, Type T, 1 phase, 200VA, 240x480V primary, 120V secondary, 50/60Hz

9070T200D1

Product availability : Stock - Normally stocked in distribution facility

Price* : 246.00 USD

Main

Product Type	Industrial Control Transformer
Power Rating	200 VA
Type	T

Complementary

Number of Phases	1 phase
Power Rating	200 VA
Temperature Rise	80 °C
Electrical Connection	Screw clamp terminals
Height	3.2 in (81.28 mm)
Width	3.75 in (95.25 mm)
Depth	3.59 in (91.19 mm)
Material	Copper winding
Fingersafe Cover Compatibility	FSC1

Environment

Certifications	UL listed file E61239 CSA file LR37055 guide 184-N-90
Enclosure Type	Not rated (open device)
Insulation Temperature	266 °F (130 °C)

Ordering and shipping details

Category	16200-9070 T (NOT TF) 50-200VA
Discount Schedule	CP8
GTIN	785901904663
Nbr. of units in pkg.	1
Package weight(Lbs)	5.60 lb(US) (2.54 kg)
Returnability	Yes
Country of origin	MX

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	3.25 in (8.255 cm)
Package 1 width	3.60 in (9.144 cm)
Package 1 Length	3.75 in (9.525 cm)
Unit Type of Package 2	PAL
Number of Units in Package 2	450
Package 2 Weight	2520.00 lb(US) (1143.052 kg)
Package 2 Height	40.00 in (101.6 cm)
Package 2 width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
PVC free	Yes

Contractual warranty

Warranty	10 Years
----------	----------