


1. STANDING FLASH 0.025 MAXIMUM PERMISSIBLE AT PARTING LINE.
2. STANDING FLASH 0.010 MAXIMUM PERMISSIBLE ALL OTHER AREAS.
3. MATERIAL SPECIFICATION:  
HIGH CONSISTENCY RUBBER (HCRP)
4. CAVITY NUMBER AND MOLDING GATES PERMITTED ON THIS SURFACE. MAXIMUM HEIGHT 0.007.



|         |       |                      |
|---------|-------|----------------------|
| 868-096 | GRAY  | .173 DIA             |
| 868-095 | BLUE  | .115 DIA             |
| PART NO | COLOR | DIA <sup>o</sup> "A" |

|                                                                                     |  |              |    |              |            |                                      |            |
|-------------------------------------------------------------------------------------|--|--------------|----|--------------|------------|--------------------------------------|------------|
| NO                                                                                  |  | COMPONENT NO |    | DESCRIPTION  |            | QTY/M                                | U/M        |
| <p align="center"><b>BILL OF MATERIAL</b></p>                                       |  |              |    |              |            |                                      |            |
|                                                                                     |  | COPIES TO    |    | MATL SPEC    | SEE NOTE 3 | FINISH                               |            |
| 1                                                                                   |  | 9            | 18 | DRW          | DHM        | DATE                                 | 05/23/08   |
| 2                                                                                   |  | 10           | 19 |              |            | SCALE                                | 2 : 1      |
| 3                                                                                   |  | 12           | 20 | CHK          |            | DATE                                 | SUPER DRW  |
| 4                                                                                   |  | 13           | 21 |              |            | DATE                                 |            |
| 5                                                                                   |  | 14           | 23 | APPD         |            | DATE                                 | RAW SIK WT |
| 6                                                                                   |  | 15           | 33 |              |            |                                      | LBS/M      |
| 7                                                                                   |  | 16           | 43 |              |            | TOLERANCE UNLESS OTHERWISE SPECIFIED |            |
| 8                                                                                   |  | 17           | 53 |              |            | TWO PLACE DEC $\pm$ .01              |            |
|                                                                                     |  |              |    |              |            | THREE PLACE DEC $\pm$ .005           |            |
|                                                                                     |  |              |    |              |            | ANGULAR $\pm$ 1°                     |            |
| <p align="center"><b>TITLE</b></p>                                                  |  |              |    |              |            |                                      |            |
| <p align="center">SEAL<br/>         SPLASH-PROOF MAXI FUSE HOLDER</p>               |  |              |    |              |            |                                      |            |
|  |  |              |    | REMOVAL<br>A |            | DRAWG. NO.<br>868-095<br>868-096     |            |
| DES PLAINES, ILLINOIS 60016                                                         |  |              |    |              |            |                                      |            |