



## TECHNICAL INFORMATION

Watts:	30
Lumens:	4100
Input Power:	AC:220-240, 50Hz
Long Life:	25,000 Hours
Unit Color:	Black
Body Type:	Die Cast Aluminium
PF:	>0.9
LED Chip Type:	SMD-Samsung Chip
CRI:	>70
Operation Temperature:	-20°C to +40°C
Dimmable:	No
Beam Angle:	100°
Color Temperature:	6500K
Dimension:	165x46x204.5mm
lumens per watt:	137
Wire Length:	35cm



## FEATURES

- Product designed with high lumen efficiency of 137 LM/W
- High quality LED SMD-Samsung Chip
- Built Strong and durable with Die Cast Aluminium - Corrosion resistant design
- Suitable for building facades, sports facilities, industrial, commercial billboards, hoardings, parking lots etc.



## 137LM BLACK SLIMLINE PRO | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

*One brand, endless solutions..*

SKU: 20403 - 30 Black

[View more details](#)



## PACKAGING

Gross Weight (Kgs):	0.72
Unit CBM:	0.002326
Dimension:	165x46x204.5mm

## MASTER BOX PACKAGING

Box Qty:	10
Length (Box) mm:	170
Width (Box) mm:	50
Height (Box) mm:	210

## LISTING DETAILS

Commodity Code:	94054210
Ean Code:	3800157666046