



TECHNICAL INFORMATION

Watts:	150
Lumens:	20500
Input Power:	AC:220-240V, 50Hz
Long Life:	25,000 Hours
Unit Color:	Black
Body Type:	Die Cast Aluminium
PF:	>0.9
LED Chip Type:	SMD-Samsung Chip
CRI:	>70
Operation Temperature:	-20°C to +40°C
Dimmable:	No
Beam Angle:	100°
Color Temperature:	4000K
Dimension:	318.5x55x390mm
lumens per watt:	137
Wire Length:	1m



FEATURES

- Product designed with high lumen efficiency of 137 LM/W
- High quality LED SMD-Samsung Chip
- Built Strong and durable with Die Cast Aluminium - Corrosion resistant design
- Suitable for building facades, sports facilities, industrial, commercial billboards, hoardings, parking lots etc.



137LM BLACK SLIMLINE PRO | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 20408 - 150 Black

[View more details](#)



PACKAGING

Gross Weight (Kgs):	3.33
Unit CBM:	0.01051
Dimension:	318.5x55x390mm

MASTER BOX PACKAGING

Box Qty:	2
Length (Box) mm:	323
Width (Box) mm:	60
Height (Box) mm:	395

LISTING DETAILS

Commodity Code:	94054210
Ean Code:	3800157666091