



## TECHNICAL INFORMATION

Watts:	50
Lumens:	5750
Input Power:	AC:220-240V, 50Hz
Long Life:	25,000 Hours
Unit Color:	Black
Body Type:	Die Cast Aluminium
PF:	>0.9
LED Chip Type:	SMD-Samsung Chip
CRI:	>70
Operation Temperature:	-20°C to +45°C
Dimmable:	No
Beam Angle:	100°
Color Temperature:	6500K
Dimension:	223x188x28mm
lumens per watt:	115

## 120LM BLACK SLIMLINE PRO | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

*One brand, endless solutions..*

SKU: 21761 - 50 Black

[View more details](#)



**SMD LED'S**

**5 YEAR WARRANTY**

High-Power LED Samsung Chip with Constant current integrated IC driver



## FEATURES

- Product designed with high lumen efficiency of 115 LM/W
- High quality LED SMD-Samsung Chip chip and high power driver
- Constant current Integrated IC driver - Built in driver - no external power supply required
- Built Strong and durable with Die Cast Aluminium - Corrosion resistant design
- Suitable for building facades, sports facilities, industrial, commercial billboards, hoardings, parking lots etc.



## PACKAGING

Gross Weight (Kgs): 0.83  
Unit CBM: 0.001948  
Dimension: 223x188x28mm

## MASTER BOX PACKAGING

Box Qty: 8  
Length (Box) mm: 30  
Width (Box) mm: 230  
Height (Box) mm: 195

## LISTING DETAILS

Commodity Code: 94054210  
Ean Code: 3800157675758